



Description

Workable on 220V 50Hz compiled in steel cabinet, Rectangular meter 110 x 90mm. Suitable for measurement of AC/ DC, Resistance 0-1000M.

Ohms in seven Ranges R.F. 0.50 Volts R.M.S. in 4 Ranges.

Accuracy : $\pm 3\%$

DC Range : 1.5, 5, 15, 50, 150, 500, 1500 F.S.D.

AC Range : 1.5, 5, 15, 50, 150, 500, 1500 F.S.D.

-

Vacuum Tube Voltmeter (V.T.V.M)

Catalog No. 101045

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.