



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Vibration Meter

Product Image



Description

Features:

--

Specifications**RT-63B**

	RT-63A	RT-63B
Measurement Range	Acceleration: 0.1-199.9m/s ² Velocity: 0.1-199.9m/s Displacement: 0.001-1.999mm P.P	Acceleration: 0.1-199.9m/s ² Velocity: 0.1-199.9m/s Displacement: 0.001-1.999mm P.P
Accuracy	±5%	±5%
Vibration Pickup	Piezoelectric ceramic accelerometer(shear-type)	Piezoelectric ceramic accelerometer(shear-type)
Measurement Frequency Rang of Acceleration	10Hz-1KHz(LO)1KHz-15KHz (HI)	10Hz-1KHz(LO)1KHz-15KHz (HI)
Measurement Frequency Rang of Velocity	10Hz-1KHz(LO)	10Hz-1KHz(LO)
Measurement Frequency Rang of Displacement	10Hz-1KHz(LO)	10Hz-1KHz(LO)
LCD Display	3.5 digits display	3.5 digits display
Single Output	AC output 2V peak(display full scale) load impedance 10K or more earphones can be connected	X
Max Hold Function	X	√
Temperature selection	X	√
Operation Condition Display	X	√
Operation Condition	0-40° C	0-40° C
Unit Size	183*67*30mm,	80*38*150mm
Standard Quantity Per Cartol	12PCS	12PCS
Standard Carton Size	51.7*40.5*32CM	51.7*40.5*32CM
Standard Carton Gross Weight	12.8KG,	14.4KG
Power	9V Battery	9V Battery

--
Vibration Meter Catalogue No. **101435**

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.