



**Address:**  
**JAMBU PERSHAD & SONS**  
6275/22 Nicholson Road,  
Ambala Cantt, Haryana,  
INDIA  
Pin: 133001

**Email:**  
sales@japson.com  
japsonambala@yahoo.com

**Website:**  
www.japson.com  
**Phone:**  
+91-171-4006897

---

# Visual Colorimeter

## Product Image

---



## Description

---

Catalog No. 100789

Visual Colorimeter - Model 790

## TECHNICAL SPECIFICATIONS

Model	LT-790
Measuring principle	Visual , in terms of international colour scale units
Modes	Transmittance, reflectance
Measurement range	0.1-79.9 Red 0.1-79.9 Yellow 0.1-49.9 Blue 0.1-3.9 Neutral
Minimum Reading	0.1
Resolution	0.1 colour scale unit
Viewing system	Fully adjustable
Light Source	Incandescent lamp
Illuminant	Approximates to daylight
Path Length	Up to 180 mm
The diffuse reflect activity of White plate	> 80%
The amplification of the magnifiers	1.9 x
The dimension of Colorimetric utensil	10 x 20 x 40mm, 25.4x20x40mm, 133.4 x 20 x 40mm
Power supply & Power Watts	AC 220 V/ 50 Hz & 50W
Weight (Gross)	13kg
Overall dimensions	620mm x 440mm x 300mm

## Disclaimer

---

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.