



Address:
JAMBU PERSHAD & SONS
6275/22 Nicholson Road,
Ambala Cantt, Haryana,
INDIA
Pin: 133001

Email:
sales@japson.com
japsonambala@yahoo.com

Website:
www.japson.com
Phone:
+91-171-4006897

Visual InfraRed Thermometer

Product Image



Description

Features:

--

- ❖ 2.5 color LCD display
- ❖ Adjustable Emissivity from 0.1 to 1.0
- ❖ Selectable color palettes
- ❖ Visual/heat map image alignment
- ❖ LED light allows the unit to be used in poor light

Specifications			
Model	RT-890		
Display	2.5 color lcd display	Color palette	Iron color, Rainbow, Black and White
RT solution	60×60 (3600 pixels)		
Visible light image resolution	300,000 pixels		
Field of view	20°×20°	Image storage	Micro SD card
Minimum Focus	0.5m	File format bmp	
Thermal sensitivity	0.15°C	Battery life 6H	
Emissivity	Adjustable 0.1~1.0	Battery type	4* 1.5V*AA* size
Temperature range	-20°~300°C/-4°~572°F		Lithium battery
Eccuracy	±2% or reading±2°C/3.6°F	Auto power off	12 Hours
Spectral band	8-14um	Working Condition	
Image frequency	6HZ	Storage Condition	
Focus mode	fixed		

--

Visual InfraRed Thermometer

Catalog No. **101411**

Disclaimer

The Products details given on this page are indicative in nature and JAPSON reserves the right to change them without prior notice. Buyer is also requested to re-check the specifications and other features of product at the time of order as product development is a continuous process and minor modifications may be made to design based on latest availability, process and design.